

designed for scientists



RV 3 V

/// Data Sheet

The rotary evaporator RV 3 is the ideal entry-level model of the IKA rotary evaporator portfolio. It finds a multitude of uses in the chemical, pharmaceutical, and biotechnology industries, in research and development, in manufacturing and quality assurance, in laboratories, and in plant construction. Thanks to specially designed glass guides, the condenser makes extremely efficient use of the 1600 cm² cooling surface.

- heating bath with 4 I volume for up to 99 °C
- water heating bath with digital temperature display and carrying handles
- mechanical lift end-point safety stop









@IKAworldwide



designed for scientists

- locking mechanism: red indicator shows unlocked position of the vapor tube
- manual lift for precise positioning of the glassware
- adjustable immersion angle
- single-handed manual lift handling, suitable for left and right-handed operators
- stepless speed setting with dial control and speed display
- speed range: 20-300rpm
- low device voltage (24V) ensures user safety
- flask clamping mechanism with integrated push-off function for easy exchange of evaporation flasks
- high-efficiency condenser with 1600 cm² cooling surface low space requirements
- compatible with the entire range of IKA RV 10 glassware







designed for scientists

Technical Data

roommoar Bata		
Type of cooling	vertical	
Cooling surface [cm2]	1600	
Motor principle	DC	
Speed range [rpm]	20 - 300	
Speed tolerance set rotation speed < 100rpm [rpm]	±1	
Speed tolerance set rotation speed > 100rpm [%]	±1	
Lift	manual	
Stroke [mm]	150	
Heating temperature range [°C]	room temp 99	
Dimensions (W x H x D) [mm]	440 x 530 x 330	
Weight [kg]	28.3	
Permissible ambient temperature [°C]	5 - 40	
Permissible relative humidity [%]	80	
Protection class according to DIN EN 60529	IP 20	
Voltage [V]	100 - 240	
Frequency [Hz]	50/60	
Power input [W]	1400	

17

